


CHARACTERISTICS

Hexamethoxymethyl-melamine resin, absorbed on a silica based on diatomaceous earth carrier

FORM OF DELIVERY

72% active resin as free flowing powder

TYPICAL STRUCTURE



FIELDS OF APPLICATION

Crosslinker for resorcinol and phenolic novolak resin types for adhesion promoting or reinforcing compounds in rubber applications

SPECIFICATION

Property

Determined per batch

Appearance

(Test Method 001)

Passes

White to tan
free flowing
powder

Ash Residue at 550 °C/2hrs.

(Test Method 003)

%

23.5 – 29.0

Moisture

(Test Method 002)

%

3 max.

Acetone Insolubles

(Test Method 068)

%

26.0 - 30.0

Fineness

% retained on 100 mesh

(Test Method 025)

%

0.10 max.

Free Formaldehyde

(Test Method DIN ISO 11402 / Calculated)

%

0.12 max.

Useful Information

Not regularly determined

Density

(@ 25 °C)

g/ml

1.4-1.5

TECHNICAL INFORMATION

Resimene 3520 S-72 is a hexamethoxymethyl melamine (HMMM) type resin used as a crosslinking agent for resorcinol or novolak resins and as an adhesion promoter for rubber compounds to steel cord, textiles and other reinforcing materials. This is a 72% active resin, absorbed on silica based on diatomaceous earth carrier, to provide for a free flowing powder.

Resimene 3520 S-72 is used in combination with resorcinol or a novolak resin for increasing compound hardness or for promotion of adhesion between rubber and reinforcing cord or fabrics. Resimene 3520 S-72 is suggested as a replacement for hexamethylene-tetramine because of its lower toxicity, absence of amine or ammoniacal by-products and minimal effect on scorch time.

Resimene 3520 S-72 is recommended to bond treated cellulose fibers to the rubber matrix. It is non-staining and non-discoloring when used on its own. When used in combination with resorcinol or resorcinol based resins, pink discoloration occurs, which becomes brown on exposure to UV light. However, the compound remains non-staining.

APPLICATION & PROCESSING

Resimene 3520 S-72 is normally used at 1.5 to 4.5 phr (active HMMM) in conjunction with 0.5 to 3.0 phr resorcinol in most elastomers to promote adhesion. It is effective with brass plated steel cord, polyester, rayon, nylon and glass fibers in tire, belting and industrial product applications. Adhesion properties can be enhanced with 5.0 to 10.0 phr silica. For hardness increase levels of resorcinol or Novolak resin can be much higher than those used for adhesion. When Resimene 3520 S-72 is used to bond treated cellulose fibers into the rubber matrix, it is usually added at about 1.5 phr (active HMMM) for each 20 to 30 phr of treated cellulose fiber. Resimene 3520 S-72 is normally added with the curatives in the final mixing stage. In the presence of resorcinol or novolak resin, the mix temperature should not exceed 100°C. Vulcanization should be taken to maximum modulus to achieve maximum adhesion or hardness.

STORAGE STABILITY:

At a temperature of 25°C the storage stability of Resimene 3520 S-72 packed in original containers amounts to at least 24 months.



Data contained in this publication are based on careful investigations and are intended for information only. Any user is obliged to carry out tests under his own responsibility as to suitability of the product for a particular use and to investigate the possible violation of industrial property rights of third parties. Information is therefore not binding and cannot be construed as guaranteeing specific properties of products as established by law. Any liability as to the exactness and completeness of data is thus excluded. We apply our General Sales Conditions.



This information is based on our present state of knowledge and is intended to provide general guideline for our products and their uses. It should not therefore be construed as guaranteeing specific properties of the products described or their suitability for a specific application. No legal liability shall be derived from it. Any existing industrial property rights must be observed. The quality of our products is guaranteed under our General Conditions of Sale.

In case of technical questions please contact: Prefere Melamines GmbH, Alt Fechenheim 34, D-60386 Frankfurt am Main, Tel.: +49 69 4109 2040

In case of commercial questions please contact: Prefere Melamines GmbH, Alt Fechenheim 34, D-60386 Frankfurt am Main, Tel.: +49 69 4109 2319

® registered trade mark
Issue: July 2019, replaces November 2011